Unlimited Options... *Extreme Dispensing*

DISPENSER DESCRIPTION	MODEL NUMBERS						
	DISPENSER ONLY	DISPENSERS WITH LOCKING ENCLOSURE/S					
		SINGLE (ONE) ENCLOSURE		DUAL (TWO) ENCLOSURES		QUAD (FOUR) ENCLOSURES	
		1 GAL / 5 LTR	2 LITER / 1/2 GAL	1 GAL / 5 LTR	2 LITER / 1/2 GAL	1 GAL / 5 LTR	2 LITER /1/2 GA
SINGLE STATION FOR 1 PRODUCT							
Bottle Fill	801GAP	801GAP-S1G	801GAP-S2L				
Bucket Fill	802GAP	802GAP-S1G	802GAP-S2L				
Bucket Fill with Remote Activation	802GAPRF	802GAPRF-S1G	802GAPRF-S2L				
SINGLE STATION WITH DIAL-A-BLEND Selector (1-4 products)							
Bottle Fill for 4 Chemicals	803GAP					803GAP-01G	803GAP-02L
Bucket Fill for 4 Chemicals	804GAP					804GAP-01G	804GAP-02L
Bucket Fill for 4 Chem. with Remote Activation	804GAPRF					804GAPRF-01G	804GAPRF-02
Bottle Fill for 1 Chemical at 4 Dilutions	805GAP	805GAP-S1G	805GAP-S2L				
Bucket Fill for 1 Chemical at 4 Dilutions	806GAP	806GAP-S1G	806GAP-S2L				
Bucket Fill for 1 Chem. at 4 Dil. w/Remote Fill	806GAPRF	806GAPRF-S1G	806GAPRF-S2L				
Bottle Fill for 4 Chem. w/ 1 Handed Fill Only	809GAP					809GAP-Q1G	809GAP-Q2L
DUAL STATION FOR 1-2 PRODUCTS							
2 Bottle Fill Ports	820GAP			820GAP-D1G	820GAP-D2L		
1 Bottle and 1 Bucket Fill Ports	822GAP	822GAP-SIG	822GAP-S2L	822GAP-D1G	822GAP-D2L		
1 Bottle and 1 Bucket Fill w/ Remote Fill	822GAPRF	822GAPRF-SIG	822GAPRF-S2L	822GAPRF-D1G	822GAPRF-D2L		
2 Bucket Fill Ports	824GAP			824GAP-D1G	824GAP-D2L		
DUAL STATION WITH DIAL-A-BLEND Selector/s (1-8 products)							
1 Bottle Fill Port with Selector (up to 4 Chem.)							
and Bucket Fill for 1 Chemical	830GAP					830GAP-01G	830GAP-02L
1 Bottle Fill Port with Selector (up to 4 Chem.) and Remote Bucket Fill for 1 Chemical	830GAPRF					830GAPRF-01G	830GAPRF-02
and hemote bucket hill for 1 Chemical 1 Bottle Fill Port with Selector 1 Chemical at	630GAPHF					6306APhr-016	6306APhr-02
4 Dilutions and Bucket Fill for 1 Chem/Dilution	832GAP	832GAP-S1G	832GAP-S2L	832GAP-D1G	832GAP-D2L		
4 Dilutions and Bucket Fill for 1 Chem/Dilution Dual Selector Valves for Bottle and Bucket	OJZUAP	0320AP-510	0320AP-52L	0320AP-010	0320AP-DZL		
	831GAP					831GAP-01G	021CAD 021
8 total products (1-4 each selector)	OSTUAP					0310AP-010	831GAP-02L
Dual Selector Valves for Bottle and Remote Bucket 8 total products (1-4 each selector)	831GAPRF					831GAPRF-01G	831GAPRF-02

NOTE: Action gap back flow preventer listed. For air gap substitute AG for GAP in part number (examples: substitute 801AG for 801GAP). Additional dispensers are available and not listed.

Additional components may be needed to run product/s at multiple dilutions. Contact DEMA customer service or your Regional Manager with any questions.

World Headquarters: DEMA Engineering Company 10020 Big Bend Blvd. • St. Louis, MO 63122 U.S.A. Tel: 1-800-325-3362 • Fax: 314-965-8319 Web site: www.demaeng.com • E-mail: sales@demaeng.com



SYDNEY, AUSTRALIA . ZEEWOLDE, THE NETHERLANDS . SHANGHAI, CHINA . SAO PAULO, BRAZIL

HAND









Remote point and fill activation is an available option on any unit

One handed bottle fill standard on all bottle fill units

The Dilution at Hand[™] (DAH) Extreme has a sleek design and enhanced color scheme that provides a modern appearance in any housekeeping environment plus multiple features to enhance productivity and dispensing flexibility. Its modular design allows the dispensers to be used with or without locking cabinets and with or without selector valves for the ultimate flexibility from 1 to 8 products or multiple dilutions for 1 plus product.

Dilution at Hand[™] Extreme features:

- Remote fill option for easy filling of buckets and scrubbers when location flexibility is required

- - Modular design allows any number of cabinets to be coupled together
 - Built-in hinges improve cabinet durability
 - Molded drip tray snaps into locking enclosure




Single Station with 1 Fill Port features 1 bottle or bucket fill tube and dilutes 1 product with a dedicated proportioner or up to 4 products or dilutions with a selector valve dial. Dual Station with 2 Fill Ports features 2 fill locations configured in 2 bottle fill, 2 bucket fill or 1 of each fill. The dual system can be configured with dedicated proportioners for 2 products, 1 selector and 1 dedicated for up to 5 products (or dilutions) or 2 selectors for up to 8 products or dilutions.

Choose Low Flow Bottle Fill, High Flow **Bucket Fill or Medium** Flow Bottle/Bucket Fill

Standard low flow bottle fill has a 1 gpm (4 lpm) flow rate and features a flow control disc for more accurate dilutions. High flow bucket fill flows at 4 gpm (15 lpm) for faster bucket filling. DEMA's unique 2.5 gpm (9.5 lpm) flow rate can be used for either bottle fill or bucket fill to provide accurate dilutions for both bottle and bucket filling when using DEMA's SafeLink Closed Loop System and in-bottle metering.







Choose Dedicated Fill Ports or **Multi-Product Selector Valve Dials**

Single or Dual Stations can use dedicated product fill ports or selector valves for up to 4 products or dilutions on a single station, 5 products / dilutions on a dual station with 1 selector and 1 dedicated port or 8 products / dilutions on a dual station with 2 selectors.

Choose Locking Enclosures, Custom Racks or

Use Alone

Modular locking enclosures are available for any DAH Extreme dispenser and are available in 1 gal (5L) or 2 liter (1/2 gal) sizes. Their modular design snaps together to form any number of product cabinets and comes with a function drip tray. And all dispensers are available mounted to a single 1 gallon or 4x1 gallon locking rack. Plus other racks for bottles from 1/2 gallon, 1 gallon and 2.5 gallon are also available.

