3524554545

The Pulsatron Series MP is a true microprocessor controlled instrument for precise and accurate metering control. Packed with standard features, the Series MP include automatic control via 4-20mA or 20-4 mA inputs, external pace with stop feature and 16 character LCD display with support for English, French, and German languages.

Nineteen distinct models are available, having pressure capabilities to 300 PSIG (21 BAR) @ 3 GPD (0.5 lph), and flow capacities to 504 GPD (79.5 lph) @ 20 PSIG (13 BAR), with a turndown ratio of 1000:1. Metering performance is reproducible to within ± 2% of maximum capacity.

Features

- Automatic Control, Fully scalable 4-20mA current signal.
- Flow Verification on select sizes.
- Flow Totalization.
- Relay Output for computer interface or AC power.
- Simple Prompts in plain language.
- Available in four languages, English, French, German, and Spanish.
- Alarm Signals for signal loss, full count, circuit failure, pulse overflow and pulse rate high.
- Liquid low-level indicator capability is standard.
- Timed Sequences can be set for selected intervals and rate for repetitive metering.
- Pulse Signals can be multiplied or divided by 1 to 999.
- Flow Rate is displayed as GPH, GPD, or LPH.
- Large easy to read backlit LCD display.

Controls



Manual Stroke Rate

Turn-Down Ratio 100:1

Stroke Length

Turn-Down Ratio 10:1

4-20mA or 20-4mA Input

- **Automatic Control**
- Fully Scalable
- Turn-Down Ratio 100:1

Flow Verification

- Monitors pump output to protect against loss of flow.
- Visual Notification.

Operating Benefits

- Reliable metering performance.
- Rated "hot" for continuous duty.
- High viscosity capability.
- Leak-free, sealless, liquid end.



Aftermarket

- **KOPkits**
- Gauges
- Dampeners
- Pressure Relief Valves
- Tanks
- **Pre-Engineered Systems**
- **Process Controllers** (MicroVision)







1 Tested and Certified by WQA









PULSAfron® Series MP **Electronic Metering Pumps**



Specifications and Model Selection

MODEL		LM K2	LMB2	LM A 2	LM D3	LMB3	LM A 3	LM K3	LMF4	LM D4	LMB4	LMH4	LM G4	LM E4	LM K5	LMH5	LMH6	LM K7	LMH7	LMH8			
Capacity	GPH	0.18	0.21	0.25	0.50	0.50	0.50	0.60	0.85	0.90	100	170	175	185	2.50	3.5	5.00	8.00	0.00	2100			
nominal	GPD	3	5	6	2	2	2	14	20	22	24	41	42	44	60	76	120	192	240	504			
(max.)	LPH	0.5	0.8	0.9	19	19	19	2.3	3.2	3.4	3.8	6.4	6.6	7.0	9.5	19	18.9	30.3	37.9	79.5			
Pressure	PSIG	300	250	150	250	150	100	100	250	150	100	250	150	100	150	50	100	50	35	20			
(max.)	BAR	21	7	10	7	0	7	7	7	-0	7	7	-0	7	0	0	7	3.3	2.4	13			
Connectio	Tubing		14" D.X3/8" OD 3/8" D.X12" OD													3/8" D.X.12" OD 12" D.X.3/4" OD (LPH8ONLY) FLOWVERFICATION (See Note)							
	Piping			14"FNPT												14"FNPT 12"FNPT							

Note: Flow Verification: A vailable on K3,B4 and E4 with connection code (H6,K7 and H7 with connection code H, 14° D x 3/8° OD only,

Engineering Data

Pump Head Materials Available: GFPPL

PVC PVDF 316 SS

Diaphragm: PTFE-faced CSPE-backed

Check Valves Materials Available:

Seats/O-Rings: PTFE

CSPE Viton

Balls: Ceramic

PTFE 316 SS Alloy C GFPPL

Fittings Materials Available:

PVC PVDF

Bleed Valve: Same as fitting and check valve

selected, except 316SS

Injection Valve & Foot Valve Assy: Same as fitting and check valve

selected

Tubing: Clear PVC White PE

Important: Material Code - GFPPL=Glass-filled Polypropylene, PVC=Polyvinyl Chloride, PE=Polyethylene, PVDF=Polyvinylidene Fluoride, CSPE=Generic formulation of Hypalon, a registered trademark of E.I. DuPont Company. Viton is a registered trademark of E.I. DuPont Company. PVC wetted end recommended for sodium hypochlorite.

Engineering Data

Reproducibility: +/- 2% at maximum capacity

Viscosity Max CPS:

For viscosity up to 3000 CPS, select connection size 3, 4, B or C with 316SS ball material. Flow rate will determine connection/ball size. Greater than 3000 CPS require spring loaded

ball checks. See Selection Guide for proper connection.

Controls: 6-Station Membrane Switch

Status Display: 16-Position LCD Dot Matrix Backilght

LED Indicator Lights, Panel Mount: Power On - Green

Pulsing - Green Flashing

Stop - Red

Stroke Frequency Max SPM: 125
External Stroke Frequency Control (Automatic):

4-20 mADC, 20-4 mADC External Pacing

Output Relay (Signal Level Option): 24 VDC, 10 mA

Output Relay (Power Option): 250 VAC, 50/60 HZ, 0.5A

Stroke Frequency Turn-Down Ratio: 100:1
Stroke Length Turn-Down Ratio: 10:1

Power Input: 115 VAC/50-60 HZ/1 ph

230 VAC/50-60 HZ/1 ph

Average Current Draw:

 @ 115 VAC; Amps:
 1.0 Amps

 @ 230 VAC; Amps:
 0.5 Amps

 Peak Input Power:
 300 Watts

 Average Input Power @ Max SPM:
 130 Watts

Custom Engineered Designs Pre-Engineered Systems

Pulsafeeder's Pre-Engineered Systems are designed to provide complete chemical feed solutions for all electronic metering applications. From stand alone simplex pH control applications to full-featured, redundant sodium hypochlorite disinfection metering, these rugged fabricated assemblies offer turn-key simplicity and industrial-grade durability. The UV-stabilized, high-grade HDPE frame offers maximum chemical compatibility and structural rigidity. Each system is factory assembled and hydrostatically tested prior to shipment.

Dimensions

	Series MP Dimensions (inches)																	
	Model No.	Α	В	В1	С	C1	ם	Е	Shpg Wt	Model No.	Α	В	B1	O	C1	D	Е	Shpg Wt
	LMA2	5.4	10.3	1	10.8	1	7.5	8.9	13	LMH4	6.2	10.9	-	11.2	ı	8.2	9.5	21
	LMA3	5.4	10.6	1	10.7	1	7.5	9.2	13	LMH5	6.2	11.3	1	11.2	1	8.2	9.9	21
	LMB2	5.4	10.3	1	10.8	1	7.5	8.9	13	LMH6	6.2	11.3	-	11.2	ı	8.2	9.9	21
	LMB3	5.4	10.6	1	10.7	1	7.5	9.2	13	LMH7	6.1	11.7	-	11.2	ı	8.2	10.3	21
	LMB4	5.4	10.6	-	10.7	-	7.5	9.2	13	LMH8*	6.1	-	10.9	-	10.6	8.2	-	25
	LMD3	5.4	10.6	1	11.2	1	7.5	9.2	15	LMK2	5.4	10.3	-	10.8	ı	7.5	8.9	13
	LMD4	5.4	10.6	1	11.2	1	7.5	9.2	15	LMK3	5.4	10.6	1	10.7	ı	7.5	9.2	13
	LME4	5.4	10.6	1	11.2	1	7.5	9.2	15	LMK5	5.4	10.9	1	11.7	1	7.5	9.5	18
	LMF4	5.4	10.6	1	11.7	1	7.5	9.2	18	LMK7	6.1	11.7	1	11.2	ī	8.2	10.3	21
	LMG4	5.4	10.6	1	11.7	1	7.5	9.2	18									

BLEED VALVE

B

B

B

C1

C1

C1

C1

NOTE: Inches X 2.54 = cm / * the LMH8 is designed without a bleed valve available

*PULSAFEEDER

27101 Airport Road Punta Gorda, FL 33982 Phone: +1(941) 575-3800 Fax: +1(941) 575-4085 www.pulsatron.com



EMP027 A17

